


ELIPSE® HALF-FACE MASK +HESPA™ A2P3 DUST (R) Filters



FILTER TECHNOLOGY





Standards

EN140: 1998 Mask Body EN14387: 2004 + A1: 2008 A2P3 R D

Efficiency

P3 >99,95% for 0,3 μ particulate At 5000 ppm: Cyclohexane (C_6H_{12}) > 35 minutes

Shelf Live

3 years (mask & filters) See storage conditions on Instructions for Use. Filters are re-usable and changeable.

Mask + Filter: net (S/M) 334 g; (M/L) 342 g gross (S/M) 435 g; (M/L) 443 g Filter: net 121 g each; both net 242 g, gross 265 g

- Mask: Medical grade TPE Conforms to ISO 10993-10: 2010 for irritations. Mask body latex and silicone free, odour free. Valve Body in Nylon, Inhalation/Exhalation diaphragm in Silicone.
- 4 point adjustable elasticated head and neck strap with comfort pad in TPE.
- Gas Filters: Activated carbon sealed into a ABS Shell. • Particulate filters: Mechanical type multi-layer HESPA Synthetic media with TPE flexible overmolded / encapsulated. Particulate filters are integrated with the carbon element.

Production

United Kingdom 100% of filters NaCl Tested

	Code	Description	Quantity
8	SPR495 (S/M) SPR496 (M/L)	A2P3 Reusable Half Mask for multiple Gases and Vapours and Dust	8 pcs. per box
The state of the s	SPR497	A2P3 replacement filters	5 sets of 2 pcs. per box
GVS	SPM009	Elipse High efficiency Mask Carry Case (Belt holder)	10 sets per box

Applications - Universal gases, dust, mist and fumes



Weldina

W: 60 mm

Metal Fumes and Dust in confined space (gas welding)



ECKER

Manufacturing

Solvents, various Organic Gases



Construction

Paint, Moulds.



Car & Ship Repair

Epoxite, Paint, Solvants



Agriculture



